
MRU D





This fifth generation roll and pitch motion sensor is specially designed for use in marine applications and is the ideal sensor for roll and pitch measurements on board ships.

Typical applications

The MRU D is specially designed for roll and pitch measurements within voyage recording, dynamic positioning systems, fishing sonars and telecommunication antenna system.

This unit has to be mounted in a fixed direction relative to the ship and is best suited for applications with limited range in roll and pitch. If unlimited mounting orientation and/or unlimited mounting range is required, we recommend one of the MRU models with sensors in all three axis. The MRU D has to be mounted with the connector pointing up or down.

Function

The unit is delivered with a Windows based configuration and data presentation software. By configuring the unit with the vector between the MRU and the vessel Center of Gravity (CG), the MRU D will output accurate roll and pitch measurements even when it is mounted high up in the ship, like on the bridge. This is due to the capability to suppress the effect of horizontal acceleration on the roll and pitch performance. This makes the unit superior to inclinometers, pendulous devices and standard Vertical Reference Units.

Each MRU D unit is delivered with a Calibration Certificate stating that the unit is tested and found within the specifications.

Variables output

The MRU D outputs roll and pitch angles and corresponding angular rate vectors fixed to the vehicle frame. The unit can in addition output surge and sway accelerations.

Digital I/O protocols

MRU data is available through both serial lines and Ethernet interface enabling easy distribution of MRU data to multiple users on board the vessel. Output data are available on two individually configurable serial lines and Ethernet/UDP. Output variables are transmitted as IEEE 32-bit floats (recommended) or as scaled integers. In addition, ASCII-based NMEA 0183 proprietary sentences can be selected as data output protocols.

FEATURES

- 0.35° roll and pitch accuracy
- Outputs real-time roll and pitch measurements
- Suppression of horizontal acceleration when mounted off the vessel Center of Gravity (CG)
- Outputs on RS-232, RS-422 and Ethernet
- High output data rate (200 Hz)
- High reliability and no scheduled maintenance, no mechanical wear-out parts
- Small size, light weight and low power consumption
- Each MRU delivered with Calibration Certificate
- Selectable communication protocols in the Windows based MRU configuration software
- Export license not required
- 2-year warranty



50000 h

1.9 kg

100000 h

Anodised aluminium

Souriau 851-36RG 16-

Ø 105 x 140 mm (4.134" x 5.525")

TECHNICAL SPECIFICATIONS

MRU D

ROLL AND PITCH OUTPUT

Angular orientation range Resolution roll, pitch Static²⁾ accuracy Dynamic¹⁾ accuracy (for a ±5° amplitude)

GYRO OUTPUT

Angular rate range ±100 °/s Angular rate noise 0.5 °/s RMS Scale factor error 0.8 % RMS

SURGE AND SWAY ACCELERATION OUTPUT

Acceleration range Acceleration noise2) Acceleration accuracy

ELECTRICAL

Voltage input Power consumption Serial ports:

Com1 Com2

Com3 & Com4

Analog channels (junction box)

Input serial line Ethernet ports Ethernet UDP/IP Output data rate (max)

Timing

±25° 0.001° 0.3° RMS

0.35° RMS

±50 m/s2 0.01 m/s2 RMS 0.05 m/s2 RMS

10 to 36 V DC Max 3 W

Bidirectional RS-422 Bidirectional RS-422 from junction box, user configurable RS-232, RS-

Input only, user config urable RS-232, RS-422 # 4, ±10V, 14 bit resolution

Two RS-232 or two RS-422

10/100 Mbps 200 Hz

OTHER DATA

MTBF (computed) MTBF (service history based) Material Connector (MIL. spec.)

WEIGHTS AND DIMENSIONS

Weight Dimensions

ENVIRONMENTAL SPECIFICATIONS Operational temperature range

Storage temperature range Enclosure protection Vibration

ELECTROMAGNETIC COMPATIBILITY

Compliance to EMCD, immunity/emission

IEC 60945/EN 60945

-5 °C to +55 °C

-25 °C to +70 °C

IEC 60945/EN 60945

1) When the MRU is exposed to a combined two-axes sinusoidal angular motion with 10 minutes duration.

 $^{2)}$ When the MRU is stationary over a 30-minute period.

Specifications subject to change without any further notice.

KONGSBERG SEATEX